

SESD 230

ESD-Simulator 30 kV

IEC / EN 61000-4-2

- 30 kV Air- and Contact discharge
- Discharge impedance 150 pF / 330 Ohm
- Contact control for contact discharge
- Counter mode with and without automatic polarity change
- With test tips for contact (SESD 3021) and air discharge (SESD 3020)



With self-test of the simulator !

Saving of cost-intensive and time-consuming intermediate calibrations. Indispensable for automatic test procedures.

Overview

The ESD Simulator SESD 230 is suitable for performing EMC tests on systems in accordance with the standard IEC / EN 61000-4-2 (ESD test). Higher test levels can be set far beyond the standard limits. Depending on the test object and test setup, two test methods are to be used: **Air discharge and Contact discharge**. In air discharge the pulse is triggered by approaching the SESD 230 towards the DUT. With the method of contact discharge the test tip of the generator is placed directly on the test object.

Important: In the case of non-contacting (e.g. painted or oxidized surface), the impulses are not triggered. The display shows "No contact". This ensures that when triggering a discharge actually takes place. The contact discharge is the favourite test method since it is most reproducible. Air discharges are used when contact discharges are not possible e.g. at plastic housings.

Key Facts

- 2 test methods are to be used: **Air discharge and Contact discharge**
- Predefined standard test levels: Higher test levels can be set far beyond the standard limits
- Displaying of the real discharge voltage at air mode
- Programmable automatic test runs
- Large display with easy to read digits
- Battery and mains operation



SESD 230


ESD-Simulator 30 kV

Technical data I

SESD Simulator 230	
Output - voltage	adjustment via digital potentiometer
Test modes	air- and contact discharge
Air discharge	0.5 kV up to 30 kV,
Contact discharge	0.5 kV up to 30 kV, 100 V steps
Polarity of the output voltage	positive and negative Special function: in "counter mode" optional polarity changeover after half of the set pulses
Charging resistance	50 MΩ
Repetition frequency	
Air discharge	single pulse or repeated (frequency depends on the distance between the discharge electrodes and the EUT)
Contact discharge	single pulse, 0.1 Hz, 0.2 Hz, 1 Hz, 2 Hz, 5 Hz, 10 Hz, 20 Hz
Continuous operation	possible at air- and contact discharge

SESD Simulator 230	
Holding time	≥ 5 sec
Pre selectable counter	1 - 9999
Discharge electrodes	according to IEC / EN 61000-4-2
Energy storage capacity	150 pF ± 10%
Discharge resistor	330 Ohm ± 5%
Operation temperature range	0 - 40° Celsius
Relative humidity	0 - 60%
Weight	app. 1470 g
Power supply	
Power supply	IN: 100-240 VAC/47-63 Hz; OUT: 9 VDC / 3 A
Weight	app. 200 g

Technical data II




SESD 230

ESD-Simulator 30 kV

Technical data III

Ideal waveform of the contact discharge current at 4 kV



Currents acc. to IEC / EN 61000-4-2, Ed. 3

Test-Level	Associated voltage level	1. peak current of discharge ($\pm 15\%$)	Rise time ($\pm 25\%$)	2. peak current of discharge ($-20\% / +40\%$)	Current after 30 ns ($\pm 30\%$)	Current after 60 ns ($\pm 30\%$)
CD AD		I_{p1}		I_{p2}		
1 1	2 kV	7.5 A	0.8 ns	4.5 A	4 A	2 A
2 2	4 kV	1.0 A	0.8 ns	9.0 A	8 A	4 A
3 --	6 kV	22.5 A	0.8 ns	13.5 A	12 A	6 A
4 3	8 kV	30.0 A	0.8 ns	18.0 A	16 A	8 A
-- 4	15 kV	56.3 A	0.8 ns	33.8 A	30 A	15 A

X*

CD = Contact discharge, AD = Air discharge

* Level "X" is a freely definable value (SESD 230 up to 30 kV air discharge and up to 30 kV contact discharge).

Scope of supply of SESD 230

- ESD simulator SESD 230
- Battery charger incl. cable
- Standard discharge electrodes for air discharge (SESD 3020)
- Standard discharge electrodes for contact discharge (SESD 3021)
- Weight (with content): approx. 3.4 kg
- Ground cable (SESD 231)
- Manual



SESD 230

ESD-Simulator 30 kV

Options	
SESD 3025	Test tip, length 50 mm, for air contact
SESD 3026	Test tip, length 50 mm with spring pin, for contact discharge
SESD 3027	Test tip, length 70 mm with spring pin, for contact discharge
SESD 3036	Hook on the generator for hanging on a balancer
SESD 231	Discharge return cable
SESD 270	HCP – Horizontal coupling plane
SESD 271	VCP – Vertical coupling plane, include earth cable SESD 272
SESD 272	Earth cable include 2 x 470 kOhm resistor, 2 m long
SESD 280	Silicon sheet: thickness 0.5 mm, resistance $3 \times 10^{15} \Omega / \text{cm}$ (IEC/EN 61000-4-2)
SESD 30 T 1000	Support arm with balancer
SESD 8800-4	ESD verification set 2 Ohm (4 GHz) to verify the ESD pulse
SESD Transport case	Transport case - ESD Verification set
SESD 30 S120	Remote control software and optical fiber set

All information regarding appearance and technical data correspond to the current state of development at the time of release of this data sheet. We reserve the right to make technical changes. 102506

